



KOSTIC

Acrylic Adhesive Film Grade 인식방법

예시)



- ① KOSTIC
- ② A: Acrylic E: Electrification
- ③ PSA film
- ④ PSA Type
- ⑤ Base Film Thickness
- ⑥ Liner Film Thickness, W: White PET
- ⑦ 개발순서

KAP – BK SERIES

KAP – CX SERIES

KAP – IM SERIES

KEP – CS SERIES

KEP – HA SERIES

www.kostic.co.kr

Sales Team Tel : +81-31-984-2100, Sales Team FAX : +81-31-982-0458



R&D Team Tel : +81-31-949-0356, R&D Team Fax : +81-31-949-0549

KOSTIC KOREA CO., LTD

KOSTIC

Silicone Adhesive Film Grade 인식방법

예시)



- ① **KOSTIC**
- ② **Protective**
- ③ **PSA film**
- ④ **Base Film Thickness, P: PI Film**
- ⑤ **Liner Film Thickness**
- ⑥ **S: Silicone PSA, B: Blue PET**
- ⑦ **Peel Strength**

KPP – S SERIES

KPP – P SERIES

www.kostic.co.kr

Sales Team Tel : +81-31-984-2100, Sales Team FAX : +81-31-982-0458

R&D Team Tel : +81-31-949-0356, R&D Team Fax : +81-31-949-0549

KOSTIC KOREA CO., LTD